



Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007T10S9 9007CS9 9007BS9 9007NS9 9007T5S9 9007AS9
Associated complete product	9007FT 9007T 9007C...S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 63.50 mm - offset: - convertible roller
Type of roller	1 steel outside roller (convertible) diameter: 35.05 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-23...85 °C
Ambient air temperature for storage	-23...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	10.2 cm
Package 1 Length	20.3 cm
Package 1 Weight	122.5 g
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.44 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------