



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch head
Device short name	9007C
Head type	Rotary head
Product compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Rotary
Type of operator	Stay put without operating lever zinc -
Type of approach	Lateral approach, 1 direction programmable
Positive opening	Without

Complementary

Switch actuation	CW and CCW From left and right
Net weight	0.19 kg


Environment

Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.355 cm
Package 1 Width	7.62 cm
Package 1 Length	49.161 cm
Package 1 Weight	185.973 g

Offer Sustainability

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------