



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007C 9007A 9007B 9007T10 9007N 9007T5
Associated complete product	9007C 9007AW
Movement of operating head	Rotary
Type of operator	Cast zinc spring return one way roller lever length: 38.10 mm - offset: - ball bearing roller
Type of roller	1 steel outside roller diameter: 16.00 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.452 cm
Package 1 Width	2.54 cm
Package 1 Length	16.387 cm
Package 1 Weight	45.359 g

Offer Sustainability

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------