

AB1FU10135U

terminal block - fixed carrier fuse 5x20 -
10mm² screw - grey



Main

Range of product	Terminal blocks
Product or component type	Terminal block
Technology type	Screw technology
Terminal block type	Fixed carrier
Product specific application	For cylindrical fuse
Fixing mode	Clip-on (35 mm asymmetrical rail) Clip-on (35 mm notched symmetrical rail) Clip-on (35 mm symmetrical DIN rail)
Nominal cross section	10 mm ²
Fuse size	5 x 20 mm
Local signalling	Without
Length	65 mm
Colour	Grey
Sale per indivisible quantity	50

Complementary

Width	12 mm
Height	69.3 Mm on 35 mm symmetrical DIN rail 73.8 Mm on 35 mm asymmetrical rail 76.8 mm on 35 mm notched symmetrical rail
Cable cross section	1...10 Mm ² , flexible cable with or without cable end 10...16 mm ² , solid cable
Tightening torque	2...2.5 N.M, M5 conforming to EN 60999 2...2.5 N.m, M5 conforming to IEC 60974-1
[Ue] rated operational voltage	250 V DC conforming to UTE category C 400 V AC conforming to UTE category C 500 V conforming to EN/IEC 60947-7-1 500 V AC conforming to VDE group C 600 V DC conforming to VDE group C 600 V, AWG 16...AWG 6 CSA 600 V, AWG 22...AWG 6 UL
[In] rated current	10 A conforming to UTE category C 15 A conforming to VDE group C 15 A, AWG 16...AWG 6 CSA 15 A, AWG 22...AWG 6 UL 3 A conforming to EN/IEC 60947-7-1
Net weight	39 g

Environment

Dielectric test voltage	6 kV conforming to EN/IEC 60947-7-1
Product certifications	CSA[RETURN]LR[RETURN]ASEV[RETURN]UL[RETURN]DNV

Contractual warranty

Warranty	18 months
----------	-----------