



Main

Module type	Processing module
-------------	-------------------

Complementary

Depth	90 mm
Discrete output current	< 7 mA
Electrical connection	Removable screw terminal block
Height	120 mm
Marking	II1 G/D-EEEx ia IIC
Mounting location	Outside dust zone
Number of inputs	2
Number of outputs	1
Power consumption in W	5 W
Product mounting	On DIN 35 mm rail
Supply circuit type	DC
[Us] rated supply voltage	24 V
Width	29.5 mm

Environment

Ambient air temperature for operation	-20...60 °C
Dust zone	Zone 20
Standards	LCIE 00ATEX6034X
Directives	2014/34/EU - ATEX directive

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

For all Reach Rohs enquiries contact us at	sustainability@tesensors.com
--	------------------------------

Contractual warranty

Warranty	18 months
----------	-----------