



Main

Module type	Processing module
-------------	-------------------

Complementary

Depth	90 mm
Electrical connection	Removable screw terminal block
Height	120 mm
Marking	II1 G/D-EEEx ia IIC
Mounting location	Outside dust zone
Number of inputs	4
Power consumption in W	5 W
Product mounting	On DIN 35 mm rail
Supply circuit type	DC
[Us] rated supply voltage	24 V
Width	29.5 mm

Environment

Ambient air temperature for operation	-20...60 °C
Dust zone	-
Standards	LCIE 00ATEX6034X
Directives	2014/34/EU - ATEX directive

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	14.5 cm
Package 1 Length	20.5 cm
Package 1 Weight	390 g

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty

18 months
