



### Main

Range of product	L100/300
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L100/300
Associated complete product	HML300 L300 HL100 ML300 HML100 ML100 L100 HL300
Movement of operating head	Rotary
Type of operator	Aluminium stay put forked arm with rollers length: 57.15 mm - offset: - adjustable angle 75° to 180° forked arm with rollers
Type of roller	2 steel outside roller diameter: 19.05 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By specific cam
Net weight	0.05 kg

### Environment

Ambient air temperature for operation	-23...85 °C
Ambient air temperature for storage	-23...85 °C
Environmental characteristic	Standard environment

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.462 cm
Package 1 Width	17.78 cm
Package 1 Length	19.304 cm
Package 1 Weight	45.359 g

### Offer Sustainability

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------