

XCRZ03

Limit switch lever, Limit switches XC Standard, XCRZ, steel square rod 6 mm, L=200 mm



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCKMR XCKVR XCRB XCRA
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 200 mm
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCRB12 XCRA15 XCRB55 XCRA12 XCRA51 XCRB52 XCKMR54D1H29 XCKMR24SR1H29 XCRA55 XCRA52 XCKMR54D2 XCRB51 XCKVR44D2H29 XCRB11 XCKVR24SR1H29 XCKVR54D1H29 XCKVR54D2H29 XCKMR54D2H29 XCRA11 XCKVR44D1H29 XCRB15 XCKMR44D1H29 XCKMR54D1 XCKMR44D2H29
Net weight	0.019 kg

Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	0.7 cm
Package 1 Length	20.0 cm
Package 1 Weight	22.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	50

Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.325 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------