


XCRZ03R

Limit switch lever, Limit switches XC Standard, XCRZ, steel square rod 6 mm, L=200 mm with red end



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCKVR XCKMR XCRA XCRB
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 200 mm with red end
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCKMR54D2H29 XCKVR44D1H29 XCKMR54D1H29 XCRB55 XCKMR24SR1H29 XCKVR44D2H29 XCKMR44D2H29 XCKMR44D1H29 XCRB52 XCKMR54D1 XCRB15 XCRB11 XCRA12 XCRB12 XCKVR24SR1H29 XCKMR54D2 XCRA11 XCRA51 XCRA15 XCRB51 XCKVR54D2H29 XCRA55 XCKVR54D1H29 XCRA52
Net weight	0.019 kg

Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.000 cm
Package 1 Width	0.800 cm
Package 1 Length	0.800 cm
Package 1 Weight	23.000 g

Unit Type of Package 2	S01
Number of Units in Package 2	50
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.290 kg

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------