

XCRZ05

Limit switch lever, Limit switches XC Special, XCRZ, large thermoplastic roller



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCRA XCRB
Movement of operating head	Rotary
Type of operator	Large roller lever thermoplastic
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCRB12 XCRA51 XCRA55 XCRB15 XCRB52 XCRB11 XCRA15 XCRB51 XCRA11 XCRA12 XCRB55 XCRA52
-----------------------------	--

Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	5.000 cm
Package 1 Length	14.200 cm
Package 1 Weight	90.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.056 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------