

XCSTR762

Guard switch, Telemecanique Safety switches
XCS, XCSTR, spindle 80 mm, 2NC+1 NO, M16



Main

Range of product	Telemecanique Safety switches XCS
Product or component type	Guard switch
Component name	XCSTR
Material	Plastic
Head type	Turret head rotary axis
Insulation	Double insulated
Type of operator	Spindle 80 mm
Electrical connection	Terminal
Contacts type and composition	1 NC + 1 NC + 1 NO
Contact operation	Slow-break, break before make
Clamping connection capacity	1 x 0.34...2 x 0.75 mm ² with or without cable end
Cable entry	2 entries tapped for M16 x 1.5
Number of poles	3

Complementary

Cable outer diameter	7...10 mm
Positive opening	With NC contact
Tripping angle	5 °
Mechanical durability	1000000 cycles
Minimum torque for tripping	0.1 N.m
Positive opening minimum torque	0.45 N.m
Minimum actuation speed	0.1 m/s
Contact code designation	B300, AC-15 (Ue = 120 V, Ie = 6 A) conforming to EN/IEC 60947-5-1 B300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (Ue = 125 V, Ie = 0.2 A) conforming to EN/IEC 60947-5-1 R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1
[Ithe] conventional enclosed thermal current	6 A
[Ui] rated insulation voltage	300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14 400 V (pollution degree 3) conforming to EN/IEC 60947-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-5-1
Maximum resistance across terminals	30 mOhm conforming to EN/IEC 60947-5-4
Short-circuit protection	6 A cartridge fuse type gG (gl)
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety reliability data	B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear
Enclosure material	Polyamide PA66 fibre glass impregnated
Lever material	Stainless steel
Width	52 mm
Height	117 mm
Depth	110 mm
Net weight	0.187 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN/IEC 60947-5-1 EN/ISO 12100 CSA C22.2 No 14 EN/IEC 60947-5-4 UL 508 EN/IEC 60204-1 EN 1088/ISO 14119
Product certifications	UL[RETURN]CSA[RETURN]BG
Protective treatment	TC TH
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	50 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to EN/IEC 61140
IP degree of protection	IP67 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.2 cm
Package 1 Width	11.6 cm
Package 1 Length	17.0 cm
Package 1 Weight	262.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------