

# XGHB221346

Electronic tag, Radio frequency identification  
XG, RFID 13.56 MHz, flat form 26 x 26 x 13  
-256 Bytes



## Main

Range of product	Telemecanique Radio frequency identification XG
Product or component type	Electronic tag
RFID electronic tag name	XGHB
RFID frequency	13.56 MHz
Design	Flat form 26 x 26 x 13
Memory capacity	256 B
Associated smart antenna	XGCS
[Sn] nominal sensing distance	40 Mm with XGCS49 42 Mm with XGCS49 + field expander XGFEC2525 55 Mm with XGCS89 55 mm with XGCS85
Outer dimension	26 x 26 x 13 mm
Quantity per set	Set of 1
Read time	12 + 0.825 x (number of 16-bit words) ms
Write time	20 + 11.8 x (number of 16-bit words) ms
IP degree of protection	IP68
Fixing mode	By screws By clips

## Complementary

Memory type	EEPROM
Memory operation	Read/write
Number of read cycles	Unlimited
Number of write cycles	100000 at -25...70 °C 2500000 at 30 °C
Maximum linear speed with "auto read/write function"	2.8 M/S with XGCS49 (read a serial number) 0.8 M/S with XGCS49 (read a word) 0.3 M/S with XGCS49 (read or write 10 words) 4.2 M/S with XGCS89 (read a serial number) 2.6 M/S with XGCS89 (read a word) 0.5 M/S with XGCS89 (read or write 10 words) 4.2 M/S with XGCS85 (read a serial number) 2.6 M/S with XGCS85 (read a word) 0.5 m/s with XGCS85 (read or write 10 words)
Data retention time	10 year(s)
Mounting location	Possible on metal support
Material	PBT (polybutylene terephthalate)
Net weight	0.025 kg

## Environment

Standards	ISO 15693
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	2 mm conforming to EN 60068-2-6 (f = 5...29.5 Hz) 7 gn conforming to EN 60068-2-6 (f = 29.5...150 Hz)
Shock resistance	30 gn conforming to EN 60068-2-27 for 11 ms
IK degree of protection	IK02 conforming to EN 50102

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	2.000 cm
Package 1 Length	6.000 cm
Package 1 Weight	21.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	25
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	762.000 g

## Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Dimensions


### Updatable Code Electronic Tags



(1) For CHC type screws


Minimum Mounting Distances

Distance Between Tags



XGCS4901201 smart antenna (format 40)		XGCS8•• smart antennas (format 80)	
e1	e2	e1	e2
50	10	120	50

Minimum Mounting Distances in a Metal Structure



(e) ≥ 20 mm.