

XUY420NA4H03M12

Photoelectric sensors XU, Roller Sensor 420 mm N4, P54 IP50 Hexa 11,2 Cable 0.3 m,M12



Main

Range of product	Telemecanique Photoelectric sensors XU
Series name	Application
Electronic sensor type	Photo-electric sensor
Sensor name	XUY
Type of output signal	Discrete
Supply circuit type	DC
Wiring technique	4-wire
Discrete output function	1 NO or 1 NC programmable
Electrical connection	1 male connector M12, 4 pins

Complementary

[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Maximum voltage drop	<2 V at 100 mA (closed state) <1 V at 10 mA (closed state)

Environment

Product certifications	CE[RETURN]cULus
Ambient air temperature for operation	0...50 °C
Ambient air temperature for storage	-20...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	10 cm
Package 1 Length	10 cm
Package 1 Weight	700 g

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com