

XUY748NB7N2

Photoelectric sensors XU, Roller Sensor 748 mm N7, P93.1 IP50 No Fix Cable 2 m,Wires



Main

Range of product	Telemecanique Photoelectric sensors XU
Series name	Application
Electronic sensor type	Photo-electric sensor
Sensor name	XUY
Type of output signal	Discrete
Supply circuit type	DC
Wiring technique	4-wire
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Cable

Complementary

[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Maximum voltage drop	<2 V at 100 mA (closed state) <1 V at 10 mA (closed state)

Environment

Product certifications	cULus[RETURN]CE
Ambient air temperature for operation	0...50 °C
Ambient air temperature for storage	-20...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.0 cm
Package 1 Length	100.0 cm
Package 1 Weight	900.0 g