

# XUZDHM10

Photoelectric sensors XU, accessory for sensor, XUM, horizontal diaphragm, Sn 1.5 m, width 1mm



## Main

|                                       |                                        |
|---------------------------------------|----------------------------------------|
| Range of product                      | Telemecanique Photoelectric sensors XU |
| Accessory / separate part category    | Sensor accessories                     |
| Accessory / separate part type        | Diaphragm                              |
| Product or component type             | Diaphragm                              |
| Installation direction                | Horizontal                             |
| Accessory / separate part destination | Miniature thru beam sensor             |
| Sale per indivisible quantity         | 2                                      |

## Complementary

|                               |            |
|-------------------------------|------------|
| [Sn] nominal sensing distance | 1.5 m      |
| Accessory dimension           | 1 x 6.4 mm |
| Net weight                    | 0.003 kg   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1.500 cm  |
| Package 1 Width              | 4.500 cm  |
| Package 1 Length             | 4.500 cm  |
| Package 1 Weight             | 2.000 g   |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 100       |
| Package 2 Height             | 3.000 cm  |
| Package 2 Width              | 19.000 cm |
| Package 2 Length             | 29.000 cm |
| Package 2 Weight             | 249.000 g |
| Unit Type of Package 3       | S02       |
| Number of Units in Package 3 | 400       |
| Package 3 Height             | 15 cm     |
| Package 3 Width              | 30 cm     |
| Package 3 Length             | 40 cm     |
| Package 3 Weight             | 1.545 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|