

ZC2JE05

Limit switch head, Limit switches XC Standard, ZC2J, without lever spring return left or right actuation



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product compatibility	XC2J
Associated lever	ZC2JY11 ZC2JY81 ZC2JY12 ZC2JY31 ZC2JY13 ZC2JY51 ZC2JY91
Associated body	ZC2JD2 ZC2JD1 ZC2JC1 ZC2JC2 ZC2JC28 ZC2JC18
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 1 direction programmable

Complementary

Switch actuation	CW or CCW From left or right
Positive opening	Without
Net weight	0.21 kg
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.700 cm
Package 1 Width	9.500 cm
Package 1 Length	4.700 cm
Package 1 Weight	215.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.242 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------