

ZCE06

Limit switch head, Limit switches XC Standard,
ZCE, cat's whisker with nitrile boot



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product Compatibility	XCKD XCKP XCKT XCMD

Associated body	ZCMD25L5 ZCD26 ZCD39 ZCMD21C12 ZCMD39L5 ZCP31 ZCMD37L5 ZCMD29L5 ZCMD21L2 ZCT21G11 ZCT27P16 ZCMD29C12 ZCT25G11 ZCT21P16 ZCMD25L1 ZCD29 ZCD21M12 ZCMD29L2 ZCT26P16 ZCMD21L1 ZCMD29L1 ZCP21M12 ZCT28N12 ZCMD61C12 ZCMD37L2 ZCMD25L2 ZCP35 ZCMD41L5 ZCT26N12 ZCMD81L2 ZCD35 ZCD29M12 ZCP39 ZCMD39L2 ZCT27G11 ZCMD69C12 ZCT25N12 ZCMD41L1 ZCP26 ZCD25 ZCD31 ZCMD39L1 ZCMD37L1 ZCMD81L5 ZCT26G11 ZCD37 ZCMD41L2 ZCT27N12 ZCMD21M12 ZCT28G11 ZCD28 ZCMD61M12 ZCP29 ZCMD21L08U78 ZCMD21L08R12 ZCP25 ZCT25P16 ZCP29M12 ZCD27 ZCP28 ZCP27 ZCT21N12 ZCMD81L1 ZCP37 ZCP21 ZCMD21L5 ZCD21 ZCT28P16
Movement of operating head	Multi-directional
Type of operator	Cat's whisker spring return metal with nitrile boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	US1000T22413
Discount Schedule	000T
GTIN	3389110191103
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	5.51 in (14.0 cm)
Package 1 Length	0.59 in (1.5 cm)
Package 1 Weight	0.49 oz (14.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	0.79 in (2 cm)
Package 2 Width	7.48 in (19 cm)
Package 2 Length	9.06 in (23 cm)
Package 2 Weight	4.94 oz (140 g)
Unit Type of Package 3	S01
Number of Units in Package 3	80
Package 3 Height	5.91 in (15 cm)
Package 3 Width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	3.26 lb(US) (1.477 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------