

ZCE08
Limit switch head, Limit switches XC Standard,
ZCE, spring rod lever nitrile boot



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product compatibility	XCKP XCKD XCMD XCKT

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated body	ZCT21P16 ZCMD37L1 ZCMD81L1 ZCP28 ZCMD21C12 ZCT27G11 ZCT25N12 ZCT27P16 ZCD31 ZCMD39L5 ZCMD37L2 ZCD26 ZCP35 ZCMD29L5 ZCMD29L1 ZCT21N12 ZCMD61M12 ZCMD39L1 ZCD35 ZCMD21L2 ZCT26G11 ZCT27N12 ZCP27 ZCP21M12 ZCMD29L2 ZCT26N12 ZCD29 ZCD21M12 ZCMD21L5 ZCT28P16 ZCT26P16 ZCP37 ZCP25 ZCMD29C12 ZCMD25L2 ZCT28G11 ZCMD21L1 ZCP31 ZCMD41L2 ZCD29M12 ZCMD39L2 ZCT25G11 ZCD25 ZCMD81L2 ZCMD37L5 ZCD21 ZCMD25L5 ZCMD61C12 ZCMD69C12 ZCT28N12 ZCMD21L08U78 ZCD27 ZCMD81L5 ZCMD41L5 ZCD28 ZCMD25L1 ZCP21 ZCT21G11 ZCP29M12 ZCMD21L08R12 ZCMD41L1 ZCMD21M12 ZCT25P16 ZCP26 ZCP29 ZCD39 ZCP39 ZCD37
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return metal (with nitrile boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	12.7 cm
Package 1 Length	1.7 cm
Package 1 Weight	24.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3 cm
Package 2 Width	13 cm
Package 2 Length	18 cm
Package 2 Weight	300 g
Unit Type of Package 3	S01
Number of Units in Package 3	80
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	1.92 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------