

ZCKE05
Limit switch head, Limit switches XC Standard,
ZCKE, without lever left and right actuation



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product compatibility	XCKJ
Associated lever	ZCKY91 ZCKY52 ZCKY53 ZCKY11 ZCKY13 ZCKY43 ZCKY51 ZCKY14 ZCKY81 ZCKY41 ZCKY59

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated body	ZCKJD37H7 ZCKJ5H29 ZCKJ8H7 ZCKJ1H29 ZCKJ8 ZCKJ7 ZCKJ41 ZCKJ6H29 ZCKJ11H29 ZCKJ41H29 ZCKJ11H7 ZCKJD35H7 ZCKJD31H7 ZCKJ9H29 ZCKJD31H29 ZCKJ21 ZCKJD39H7 ZCKJ9H7 ZCKJ4H29 ZCKJD35H29 ZCKJ6 ZCKJ11 ZCKJ5 ZCKJ7H29 ZCKJ1H7 ZCKJ7H7 ZCKJ9 ZCKJ8H29 ZCKJ6H7 ZCKJ4104H29 ZCKJD31 ZCKJ4104H7 ZCKJ5H7 ZCKJ2H7 ZCKJ404H29 ZCKJD37H29 ZCKJ4 ZCKJ21H7 ZCKJ1 ZCKJ2H29 ZCKJD39H29 ZCKJD37 ZCKJ2 ZCKJD35 ZCKJ41H7 ZCKJ404 ZCKJD39 ZCKJ4104 ZCKJ21H29 ZCKJ4H7 ZCKJ404H7
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Switch actuation	From left and/or right CW and/or CCW
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.200 cm
Package 1 Width	4.600 cm
Package 1 Length	8.700 cm
Package 1 Weight	168.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	27
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.794 kg
Unit Type of Package 3	P06
Number of Units in Package 3	864
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	160.852 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------