

# ZCKE65

Limit switch head, Limit switches XC Standard, ZCKE, metal side plunger with vertical roller



## Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ2H29 ZCKJD31 ZCKJ8H29 ZCKJ21H29 ZCKJD37H7 ZCKJ7 ZCKJD37H29 ZCKJ9H29 ZCKJ2 ZCKJ7H7 ZCKJ21 ZCKJD35H7 ZCKJD31H7 ZCKJ8 ZCKJ5 ZCKJD39 ZCKJ11H7 ZCKJ1 ZCKJ11H29 ZCKJ2H7 ZCKJ11 ZCKJ9 ZCKJ6 ZCKJ1H29 ZCKJ8H7 ZCKJ21H7 ZCKJ5H29 ZCKJ9H7 ZCKJ6H7 ZCKJD35 ZCKJ7H29 ZCKJD37 ZCKJD35H29 ZCKJD39H7 ZCKJ1H7 ZCKJD31H29 ZCKJD39H29 ZCKJ5H7 ZCKJ6H29
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with vertical roller)
Type of approach	Vertical approach, 2 directions

## Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

## Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.100 cm
Package 1 Width	4.600 cm
Package 1 Length	8.600 cm
Package 1 Weight	186.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.680 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------