

ZCKE66

Limit switch head, Limit switches XC Standard, ZCKE, steel ball bearing plunger



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJD39 ZCKJ6H29 ZCKJ9H29 ZCKJ8 ZCKJ5H7 ZCKJD37H29 ZCKJ2H7 ZCKJ41 ZCKJ1 ZCKJD31H7 ZCKJ21 ZCKJ5 ZCKJD35H7 ZCKJ2 ZCKJD39H29 ZCKJ7 ZCKJ2H29 ZCKJ8H29 ZCKJ41H7 ZCKJ4H7 ZCKJ9 ZCKJ11H7 ZCKJ6 ZCKJ8H7 ZCKJ11H29 ZCKJ9H7 ZCKJ1H29 ZCKJ1H7 ZCKJ5H29 ZCKJD35H29 ZCKJD31H29 ZCKJ6H7 ZCKJD37 ZCKJ41H29 ZCKJ4H29 ZCKJD39H7 ZCKJ21H7 ZCKJ7H29 ZCKJD35 ZCKJD37H7 ZCKJ7H7 ZCKJD31 ZCKJ21H29 ZCKJ4 ZCKJ11
Movement of operating head	Linear
Type of operator	End plunger spring return metal (ball bearing mounted)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.700 cm
Package 1 Width	8.600 cm
Package 1 Length	4.200 cm
Package 1 Weight	145.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	48
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.324 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------