

# ZCKY52

Limit switch lever, Limit switches XC Standard,  
ZCKY, glass fiber round 3 mm L=125 mm,  
-40...120 °C



## Main

|                            |  |
|----------------------------|--|
| Range of product           | Telemecanique Limit switches XC Standard                         |
| Series name                | Standard format  |
| Product or component type  | Limit switch lever   |
| Device short name          | ZCKY   |
| Product compatibility      | XCKJ   |
| Associated head            | ZCKE05   |
| Movement of operating head | Rotary   |
| Type of operator           | Rod lever spring return glass fiber (round rod 3 mm, L = 125 mm) |
| Type of approach           | Lateral approach   |

## Complementary

|                  |                    |
|------------------|--------------------|
| Switch actuation | By any moving part |
| Positive opening | Without            |

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -25...70 °C for standard environment<br>-40...70 °C for low temperature<br>10...120 °C for high temperature |
| Ambient air temperature for storage   | -40...70 °C standard environment<br>-40...70 °C low temperature<br>10...120 °C high temperature             |
| Environmental characteristic          | Low temperature<br>Standard environment<br>High temperature   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 2.000 cm  |
| Package 1 Width              | 1.500 cm  |
| Package 1 Length             | 12.500 cm |
| Package 1 Weight             | 15.000 g  |
| Unit Type of Package 2       | S01       |
| Number of Units in Package 2 | 20        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 15.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 461.000 g |

## Offer Sustainability

|  |   |
|--|---|
| Sustainable offer status                   | Green Premium product   |
| Circularity Profile                        | No need of specific recycling operations  |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|