

ZCKY715

Limit switch lever, Limit switches XC Standard, ZCKY, forked arm with rollers 1 track, 10...120 °C



ZCKY71

Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ
Associated head	ZCKE09
Movement of operating head	Rotary
Type of operator	Stay put forked arm with rollers stay put thermoplastic (1 track)
Type of approach	Lateral approach

Complementary

Switch actuation	By specific cam
Positive opening	Without

Environment

Ambient air temperature for operation	10...120 °C for high temperature
Ambient air temperature for storage	10...120 °C high temperature
Environmental characteristic	High temperature

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	10.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	35.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------