

ZCKY91

Limit switch lever, Limit switches XC Standard, ZCKY, spring rod with metal end, -40...70 °C



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ XCKS XCKL XCKM
Associated head	ZCKD05 ZCKE05
Movement of operating head	Rotary
Type of operator	Spring rod lever spring return (with metal rod)
Type of approach	Lateral approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature
Ambient air temperature for storage	-40...70 °C standard environment -40...70 °C low temperature
Environmental characteristic	Standard environment Low temperature

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.100 cm
Package 1 Width	2.200 cm
Package 1 Length	17.000 cm
Package 1 Weight	23.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	60
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.675 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------