



Main

Accessory / separate part designation	Cover and indicator light module
Accessory / separate part destination	XCKJ (fixed body)
Accessory / separate part category	Visualisation application
Accessory / separate part type	1 LED

Complementary

Network type	DC
[Ue] rated operational voltage	24 V
Voltage range	20...30 V
Service life in hours	100000 h
Reverse polarity protection	Yes

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.900 cm
Package 1 Width	5.000 cm
Package 1 Length	9.700 cm
Package 1 Weight	64.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	60
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	4.140 kg

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------