

ZCMD21M12

Limit switch body, Limit switches XC Standard, ZCMD, 1C/O, silver, snap action, connection, M12



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch body
Device short name	ZCMD
Design	Miniature
Body type	Fixed
Associated head	ZCE29 ZCE02 ZCE06 ZCE62 ZCE09 ZCE13 ZCE67 ZCE10 ZCE14 ZCE07 ZCE08 ZCE65 ZCEG1 ZCEF0 ZCE24 ZCE11 ZCE27 ZCE64 ZCEF2 ZCE28 ZCE66 ZCE01 ZCE63 ZCE21
Body material	Zamak
Number of poles	2
Contacts type and composition	1 C/O
Contact operation	Snap action

Complementary

Product Compatibility	XCMD
Electrical connection	Male connector M12, 4 pins
Contacts insulation form	Za
Contacts material	Silver plated contacts
Positive opening	Without
Minimum actuation speed	0.01 m/min
[Ie] rated operational current	0.1 A 250 V, DC-13 IEC 60947-5-1 appendix A 1.5 A 240 V, AC-15 IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	3 A
[Ui] rated insulation voltage	300 V 3)UL 508 300 V 3)CSA C22.2 No 14 250 V 3)IEC 60947-5-1
Maximum resistance across terminals	25 mOhm IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	2.5 KV IEC 60664 2.5 kV IEC 60947-1
Short-circuit protection	4 A cartridge fuse gG

Electrical durability	5000000 Cycles, DC-13 24 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 48 V, 2 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13 120 V, 1 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C
Width	1.18 in (30 mm)
Height	1.97 in (50 mm)
Depth	0.63 in (16 mm)
Net Weight	0.14 lb(US) (0.065 kg)

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
-------------------------------------	----------------------------

Ordering and shipping details

Category	US1000T22413
Discount Schedule	000T
GTIN	3389110299144
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.67 in (1.7 cm)
Package 1 Width	2.09 in (5.3 cm)
Package 1 Length	2.09 in (5.3 cm)
Package 1 Weight	2.68 oz (76.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	60
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	11.05 lb(US) (5.01 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	1920
Package 3 Height	29.53 in (75 cm)
Package 3 Width	23.62 in (60 cm)
Package 3 Length	31.50 in (80 cm)
Package 3 Weight	374.79 lb(US) (170 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------