

ZCY19

Limit switch lever, Limit switches XC Standard, ZCY, steel roller



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKT XCMD XCKD XCKP
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal
Tracks	20/36 mm for XCMD 24/40 mm for XCKD 24/40 mm for XCKP 24/40 mm for XCKT
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	2.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	23 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	39 cm
Package 2 Width	82 cm
Package 2 Length	97 cm
Package 2 Weight	232 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	2.667 kg

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------