

ZCY45

Limit switch lever, Limit switches XC Standard, ZCY, thermoplastic roller variable length



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch lever
Device short name	ZCY
Product Compatibility	XCKT XCMD XCKP XCKD
Associated head	ZCE05 ZCE01
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic variable length)
Tracks	No track
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	US1000T22413
Discount Schedule	000T
GTIN	3389110191967
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.35 in (0.9 cm)
Package 1 Width	0.59 in (1.5 cm)
Package 1 Length	4.06 in (10.3 cm)
Package 1 Weight	0.78 oz (22 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	15.35 in (39 cm)
Package 2 Width	41.34 in (105 cm)
Package 2 Length	60.63 in (154 cm)
Package 2 Weight	0.49 lb(US) (0.224 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------