



Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	1
Device application	Light control
Provided equipment	Internal power connection
Colour tint	White

Complementary

Rated current	10 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm
Net weight	0.0174 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	LV directive EMC directive EN 60669-1

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Acetone Bleach Window-cleaning fluid Petrol Alcohol Liquid soap Oil UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	6.5 cm
Package 1 Length	6.5 cm
Package 1 Weight	20 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.4 cm
Package 2 Width	13.6 cm
Package 2 Length	33.5 cm
Package 2 Weight	274 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.775 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------