

Product data sheet

Characteristics

NSYBCE8

Spacial SF brush flexible cable entry gaskets - 25 mm - 800 mm enclosure



Local distributor code: 22145040
EAN Code: 3606485130064



Main

| | |
|------------------------------------|---------------------------------------|
| Range | Spacial |
| Product or component type | Brush gasket |
| Accessory / separate part category | Cable management accessory |
| Device application | Multi-purpose |
| Range compatibility | Spacial Spacial SF suitable enclosure |
| Device composition | 2 gasket |
| Quantity per set | Set of 1 |

Complementary

| | |
|------------------|---------------------------------|
| Mounting support | Cable gland plate |
| Cable entry | 1 or 2 entries |
| Fixing mode | Clipped |
| Height | 70 mm |
| Width | 800 Mm nominal: 735 mm real: |
| Depth | 25 mm |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.0 cm |
| Package 1 Width | 8.0 cm |
| Package 1 Length | 74.0 cm |
| Package 1 Weight | 426.0 g |
| Unit Type of Package 2 | P12 |
| Number of Units in Package 2 | 120 |
| Package 2 Height | 105.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 92.2 kg |

Offer Sustainability

| | |
|--------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |

| | |
|----------------------------|---|
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Logistical informations

| | |
|-------------------|----|
| Country of origin | FR |
|-------------------|----|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|