Product data sheet
Characteristics

PKF32M423
Priza Mobila Mureva, Dreapta, 32 A, 2P + E, 200, 250 V Ac, Ip44

Principal

Gama	Mureva
Tip produs sau componenta	Wander socket
Nume scurt al dispozitivului	Mureva screw
Plug, socket category	Low voltage
Descriere poli	2P + E
Tip retea electrica	C.a.
Standard priza	Industrial

Suplimentar

Forma fisa, priza, carcasa	Drept
[In] calibru	32 A
[Ue] tensiune nominala	200...250 V
Frecventa retea electrica	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Carcasa self-extinguishing engineering polymer
Materialul contactelor	Sleeves brass
Conexiuni - borne	Captive screws
Sectiune cablu	2,5…10 mm²
Diametru exterior cablu	11,5…21 mm
Intrare cablu	Presetupa Fair lead
Tip filet	Pg 21
Greutate neta	0,25 kg
Inaltime	98 mm
Latime	98 mm
Adancime	165 mm
Culoare	Gri (RAL 7035)
Voltage colour	Blue

Mediu

Standarde	IEC 60309-1 IEC 60309-2
Grad de protectie IP	IP44 conformitate cu SR EN 60529
Grad de protectie IK	IK08 conforming to EN 62262
Rezistenta la foc	850 °C conformitate cu IEC 60695-2-1
Umiditate relativa	50 % la 40 °C 70 % la 30 °C 90 % la 20 °C
Temperatura ambientala de utilizare	35 °C 86400 s) -25…40 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	6,5 cm
Latime prima forma de impachetare	9,5 cm
Lungime prima forma de impachetare	17,0 cm
Greutate prima forma de impachetare	223,0 g
Unitate de masura pentru a doua forma de impachetare	BB1
Numar unitati in a doua forma de impachetare	10
Inaltime a doua forma de impachetare	17,0 cm
Latime a doua forma de impachetare	26,0 cm
Lungime a doua forma de impachetare	27,0 cm
Greutate a doua forma de impachetare	2,3 kg
Unitate de masura pentru a treia forma de impachetare	S03
Numar unitati in a treia forma de impachetare	20
Inaltime a treia forma de impachetare	30,0 cm
Latime a treia forma de impachetare	30,0 cm
Lungime a treia forma de impachetare	40,0 cm
Greutate a treia forma de impachetare	5,28 kg

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	Declaratia REACH
Directiva RoHS UE	Conform cu anumite exceptii
Regulamentul RoHS China	Declaratia RoHS China
Informatii privind scutirea de la RoHS	Da
Raport de mediu	Profilul Ambiental Al Produsului
Profil circularitate	Nu sunt necesare operatii de reciclare speciale

Garan□ie contractuală

Garantie	18 luni