Product data sheet
Characteristics

NSYCCOHY230VID
Climasys CC - electronic hygrostat - 200…240 V - Hr 20…80% - OLED screen

Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Electronic hygrostat
Humidity setting range	20…80 %
Display type	OLED screen
Information displayed	Relative humidity

Complementary

Input voltage	200...240 V AC
Maximum switching capacity	4 A 230 V AC
Electrical connection	6 terminals, clamping capacity: 2.5 mm²
Mounting mode	By screws Clipped
Height	85 mm external:
Width	56 mm external:
Depth	44 mm external:
Mounting location	On mounting plate Cross rails 35 mm DIN rail Spacial upright
Ambient air temperature for operation	-40…80 °C
Hysteresis	3 %
Number of outputs	2 heating function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.096 cm
Package 1 Width	7.62 cm
Package 1 Length	8.636 cm
Package 1 Weight	149.687 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 mois