

# Product data sheet

## Characteristics

# LA9F703

TeSys F - terminal shroud for contactor or relay  
2P/3P



Local distributor code: 2197814  
EAN Code: 3389110120622



## Main

|                                    |  |
|------------------------------------|--|
| Range                              | TeSys  |
| Device short name                  | LA9F   |
| Product or component type          | Terminal shroud  |
| Accessory / separate part category | Protection accessory   |
| Range compatibility                | TeSys LR9F electronic thermal overload relay<br>TeSys LC1F contactor<br>TeSys LC2F reversing contactor<br>TeSys CR1F magnetic latching contactor<br>Altistart ATS22 soft starter                         |
| Product compatibility              | LC1F225, F265, F330, F400, F500<br>LC1F4002, F5002<br>CR1F265, F400, F500<br>ATS22 C21, C25, C32, C41, C48, C59<br>LC2F225, F265<br>LR9F7575, F7579, F7581<br>LR9F75, F79, F81<br>LR9F7375, F7379, F7381 |
| Quantity per set                   | Set of 6   |
| Poles description                  | 1P   |







## Complementary

|                   |                   |
|-------------------|-------------------|
| Mounting location | On power terminal |
| Net weight        | 0.25 kg           |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 10.900 cm |
| Package 1 Width              | 15.700 cm |
| Package 1 Length             | 33.500 cm |
| Package 1 Weight             | 390.000 g |
| Unit Type of Package 2       | P06       |
| Number of Units in Package 2 | 39        |
| Package 2 Height             | 75.000 cm |
| Package 2 Width              | 60.000 cm |
| Package 2 Length             | 80.000 cm |
| Package 2 Weight             | 28.483 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#"> EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile        | <a href="#"> End Of Life Information</a>       |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins     |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|