


Tehničke karakteristike proizvoda

Karakteristike

33659

naponski okidač MX ili XF - 24..30 V DC/AC 50/60 Hz



Osnovne informacije

Grupa proizvoda	ComPacT
Grupa proizvoda	ComPacT NS630b...1600 new generation ComPacT NS1600b...3200 new generation
Kratko ime uređaja	MX
Tip proizvoda ili komponente	Naponski okidač
Primena uređaja	Upravljanje
Tip naponskog okidača	Kalem za isključenje Trenutni naponski okidač
Tip upravljanja	Standardni
Napon upravljačkog kola	24 V AC 50 Hz 24...30 V DC
Circuit breaker mounting mode	Fiksno
Kompatibilnost grupe proizvoda	Compact Compact NS630b...1600 Compact Compact NS1600b...3200

Dopunske informacije

Operating threshold	0.7...1.1 x Un otvaranje
Vreme odziva	50 ms +/- 10 % za Compact NS630b...1600 50 ms +/- 10 % za Compact NS1600b...3200 55 ms +/- 10 % za Masterpact NT 70 ms +/- 10 % za Masterpact NW
Snaga držanja	4.5 VA
Pribor / posebna kategorija	Rezervni deo za Masterpact NT Rezervni deo za Masterpact NW Rezervni deo za ComPacT NS630b...1600 new generation Rezervni deo za ComPacT NS1600b...3200 new generation

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,3 cm
Package 1 Width	6,0 cm
Package 1 Length	8,4 cm
Package 1 Weight	150,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,0 cm
Package 2 Width	18,5 cm
Package 2 Length	13,2 cm
Package 2 Weight	1,57 kg
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm

Package 3 Length	40,0 cm
Package 3 Weight	19,303 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 meseci
-----------	-----------