

Product data sheet

Characteristics

LAD6K10EN

Bloc auxiliar TeSys - 60...72 V c.c./c.a. 50...60 Hz



Principal

Gama	TeSys
Tip produs sau componenta	Bloc de zavoare mecanice
Compatibilitate produs	LC1D40A...D65A Relee de control TeSys D LC1DT60A...DT80A LC1DT20...DT40 LC1D09...D38
[Uc] control circuit voltage	60/72 V c.a. 50/60 Hz 60/72 V c.c.

Suplimentar

Locul de montare	Partea frontala
Control declansare	Manual Electric
[Ui] tensiune nominala de izolatie	690 V conformitate cu SR EN 60947-5-1
Puterea ceruta in VA	25 pentru c.a. circuit
Puterea ceruta in W	30 W pentru c.c. circuit
Durabilitate mecanica	500000 cic
Viteza maxima de functionare	1200 cic/h
Factor de sarcina	10 %
Greutate produs	0,07 kg

Mediu

Certificari produs	UL CSA
Grad de protectie IP	IP2x conformitate cu VDE 0106
Tratament protector	TH conformitate cu IEC 60068
Temperatura ambientala de functionare	-25...55 °C
Temperatura de depozitare	-40...80 °C

Packing Units

Tip unitate a formei de impachetare 1	PCE
Număr de produse în pachet	1
Greutate colet(Lbs)	95 g
Inaltimea formei de impachetare 1	5,3 cm
Latimea formei de impachetare 1	5 cm
Lungimea formei de impachetare 1	6,5 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Stare ofertă sustenabilă	Produs Green Premium
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Informatii privind scutirea de la RoHS	Da
Regulamentul RoHS China	Declaratia RoHS China
Raport de mediu	Profilul Ambiental Al Produsului
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Contractual warranty

Garantie	18 months
----------	-----------