

Tehničke karakteristike proizvoda

Karakteristike

EPH9900121

Asfora - dvostruka utičnica sa uzemljenjem sa strane - 16A bela



Osnovne informacije

Seriya	Asfora
Tip proizvoda ili komponente	Utičnica
Broj utičnica	2
Konfiguracija polova utičnice	2P + E
Nijansa boje	Bela
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Prezentacija uređaja	Kompletan proizvod
Montaža uređaja	Ugradno
Način fiksiranja	Kukicama54...72 mm
Standard utičnice	CEE 7/3
Outlet standard deviation	Šuko
Opis standarda utičnice	Uzemljenje sa strane
Opseg snage	3680 W
Nazivna struja	16 A pri 250 V AC
Završna obrada	Sjajno
Materijal	ABS (akrilonitril-butadien-stiren): dekorativni ram ASA + PC: centralna pločica
Dužina ogoljenog dela žice	11 mm
Provodni materijal	Bakar
Povezivanje - priključci	Vijčani priključci
Broj kablova	2 kabl(ovi) 2,5 mm²
Krutost kabla	Jednožični višezični Krući Fleksibilni
Količina po setu	1
Ip stepen zaštite	IP20
Projektovana dubina	23 mm
Širina	83 mm
Visina	123 mm
Dubina	46 mm

Okruženje

Standardi	IEC 60884-1
Sertifikacija proizvoda	VDE[RETURN]UKR

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,500 cm
Package 1 Width	9,000 cm
Package 1 Length	12,500 cm
Package 1 Weight	102,300 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	10,000 cm
Package 2 Width	20,000 cm
Package 2 Length	31,500 cm
Package 2 Weight	1,125 kg
Unit Type of Package 3	S04
Number of Units in Package 3	50
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	6,536 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------