




### Main

|                               |                                                                                     |
|-------------------------------|-------------------------------------------------------------------------------------|
| Range                         | MasterPacT                                                                          |
| Range of product              | MasterPact NT<br>MasterPact NW<br>MasterPact NW DC                                  |
| Device short name             | MX                                                                                  |
| Product or component type     | Voltage release                                                                     |
| Device application            | Control                                                                             |
| Voltage release type          | Opening coil<br>Instantaneous voltage release                                       |
| Control type                  | Standard                                                                            |
| [Uc] control circuit voltage  | 200...250 V AC 50/60 Hz<br>200...250 V DC                                           |
| Circuit breaker mounting mode | Fixed                                                                               |
| Range compatibility           | Masterpact MasterPact NT<br>Masterpact MasterPact NW<br>Masterpact MasterPact NW DC |

### Complementary

|                      |                                                                      |
|----------------------|----------------------------------------------------------------------|
| Operating threshold  | 0.7...1.1 x Un opening                                               |
| Response time        | 50 ms +/- 10 % for MasterPact NT<br>50 ms +/- 10 % for MasterPact NW |
| Supply holding power | 4.5 VA                                                               |

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 5.000 cm   |
| Package 1 Width              | 6.000 cm   |
| Package 1 Length             | 8.500 cm   |
| Package 1 Weight             | 173.000 g  |
| Unit Type of Package 2       | S02        |
| Number of Units in Package 2 | 20         |
| Package 2 Height             | 15.000 cm  |
| Package 2 Width              | 30.000 cm  |
| Package 2 Length             | 40.000 cm  |
| Package 2 Weight             | 3.720 kg   |
| Unit Type of Package 3       | P12        |
| Number of Units in Package 3 | 320        |
| Package 3 Height             | 45.000 cm  |
| Package 3 Width              | 80.000 cm  |
| Package 3 Length             | 120.000 cm |
| Package 3 Weight             | 71.520 kg  |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                    |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                              |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                             |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                      |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                            |
| California proposition 65  | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|