

Tehničke karakteristike proizvoda Karakteristike

NU342918 USB 3.0 utičnica 1 modul bela



Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	USB konektor
Tip priključka	USB 2.0
Tip električnog kola	Podaci
Prezentacija uređaja	Mehanizam
Nijansa boje	Bela (RAL 9003)
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Broj utičnica	1
Način pričvršćivanja	Utično
Broj modula	1 modul
Završna obrada	Sjajno
Količina po setu	Set od 10
Povezivanje - priključci	Vijčani priključci
Kapacitet priključaka	$\leq 1.5 \text{ mm}^2$ za fleksibilni kabl(ovi) $\leq 1.5 \text{ mm}^2$ za kruti kabl(ovi)
Dužina ogoljenog dela žice	8 mm
Materijal	Termoplastika ABS-UV stabilizovana: centralna pločica PC (polikarbonat) GF10 FR: kućište
Visina	45 mm
Širina	22,5 mm
Dubina	28 mm
Dubina za ugradnju	19,7 mm
Masa proizvoda	0,014 kg
Direktive	2014/30/EU - elektromagnetna kompatibilnost
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Temperatura okoline za skladištenje	-5...50 °C
Temperatura okoline za rad uređaja	5...45 °C
Standardi	EN 62680-2-1 EN 61000-6-1 EN 61000-6-3
Ip stepen zaštite	IP2XC
Ik stepen zaštite	IK02

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,3 cm
Package 1 Width	3,0 cm
Package 1 Length	4,5 cm
Package 1 Weight	18,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,0 cm
Package 2 Width	14,0 cm
Package 2 Length	26,0 cm
Package 2 Weight	264,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	1,63 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.