

Tehničke karakteristike proizvoda Karakteristike

NU349754

Telefonska utičnica RJ12 2 modula antr



Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Telefonska utičnica
Primena uređaja	Komunikacija
Prezentacija uređaja	Mehanizam
Nijansa boje	Antracit (RAL 7021)
Tip telefonske utičnice	RJ12 (6 kontakti) - kategorija 3 pri 16 Mbit/s

Dopunske informacije

Broj utičnica	1
Broj modula	2 modula
Povezivanje - priključci	Vijčani priključci upredene parice
Montaža uređaja	Ugradno
Način fiksiranja	Utično
Materijal	Termoplastika ABS-UV stabilizovana: centralna pločica
Dubina	34 mm
Širina	45 mm
Visina	45 mm
Dubina za ugradnju	34 mm
Temperatura okoline za rad uređaja	-25...55 °C
Temperatura okoline za skladištenje	-25...55 °C
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ip stepen zaštite	IP20
Ik stepen zaštite	IK01

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,5 cm
Package 1 Width	4,5 cm
Package 1 Length	4,5 cm
Package 1 Weight	257,0 g

Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,8 cm
Package 2 Width	14,2 cm
Package 2 Length	26,0 cm
Package 2 Weight	288,0 g
Unit Type of Package 3	S03
Number of Units in Package 3	100
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	3,302 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.