

ZCE05

Limit switch head, Limit switches XC Standard, ZCE, without lever spring return left or right actuation



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product compatibility	XCKT XCMD XCKP XCKD
Associated lever	ZCY18 ZCY26 ZCY59 ZCY19 ZCY25 ZCY12 ZCY15 ZCY22 ZCY54 ZCY55 ZCY17 ZCY48 ZCY69 ZCY44 ZCY45 ZCY49 ZCY46 ZCY53 ZCY91 ZCY16 ZCY39 ZCY23 ZCY81

Associated body	ZCP26 ZCMD21L08U78 ZCP29 ZCT25P16 ZCMD21M12 ZCMD21L08R12 ZCP29M12 ZCMD41L1 ZCP21 ZCMD25L1 ZCD31 ZCMD81L5 ZCD35 ZCT25G11 ZCMD25L5 ZCD27 ZCMD69C12 ZCMD37L2 ZCMD61C12 ZCD28 ZCT28N12 ZCD21 ZCMD29L5 ZCMD21L5 ZCMD37L5 ZCMD39L2 ZCP39 ZCP27 ZCD26 ZCT27N12 ZCMD29L1 ZCP35 ZCT27G11 ZCMD81L1 ZCMD37L1 ZCT21P16 ZCD29M12 ZCP31 ZCMD41L2 ZCD39 ZCMD39L5 ZCT25N12 ZCT28G11 ZCP28 ZCT27P16 ZCMD21L1 ZCT28P16 ZCD29 ZCP25 ZCMD25L2 ZCT26N12 ZCD37 ZCD21M12 ZCMD29L2 ZCP21M12 ZCP37 ZCT26P16 ZCT21N12 ZCMD29C12 ZCMD61M12 ZCT26G11 ZCMD21L2 ZCMD39L1 ZCMD21C12 ZCT21G11 ZCMD41L5 ZCD25 ZCMD81L2
Movement of operating head	Rotary
Type of operator	Without operating lever spring return metal
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Positive opening	With
Net weight	0.045 kg

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	3.3 cm
Package 1 Length	3.0 cm
Package 1 Weight	42.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------