

ZCKE08

Limit switch head, Limit switches XC Standard, ZCKE, spring rod



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Multi-directional head
Product compatibility	XCKJ
Associated body	ZCKJ6H29 ZCKJD31H29 ZCKJD39H29 ZCKJ5H7 ZCKJD37H29 ZCKJD31 ZCKJ21 ZCKJ9H29 ZCKJ7 ZCKJ5 ZCKJ5H29 ZCKJ1H29 ZCKJ2H7 ZCKJ21H29 ZCKJ21H7 ZCKJ1 ZCKJD39 ZCKJ11H7 ZCKJ2 ZCKJ8 ZCKJ8H29 ZCKJD39H7 ZCKJD35 ZCKJ9H7 ZCKJD37 ZCKJ2H29 ZCKJ6H7 ZCKJ6 ZCKJ9 ZCKJ8H7 ZCKJD31H7 ZCKJD35H7 ZCKJ11 ZCKJ11H29 ZCKJ7H7 ZCKJD35H29 ZCKJ1H7 ZCKJD37H7 ZCKJ7H29
Movement of operating head	Multi-directional Rotary
Type of operator	Spring rod spring return
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.600 cm
Package 1 Width	3.600 cm
Package 1 Length	15.600 cm
Package 1 Weight	134.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	18
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.740 kg
Unit Type of Package 3	P06
Number of Units in Package 3	288
Package 3 Height	45.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	49.828 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------