

## Product data sheet

### Characteristics

# GCKR50A2G

Exclusive - 2-pole switch - 2 gang - 50 A - white



### Main

Product or component type	Switch
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 5

### Complementary

Switch function	2-pole
Control type	Dolly switch
Number of gangs	2 gangs
Pilot light	Without neon indicator
Device mounting	Wall mounted
Rated current	50 A at 230 V AC
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Surface finish	Matt
Height	86 mm
Width	146 mm
Depth	36 mm
Net weight	0.208 kg

### Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------