



Main

Product brand	Clipsal
Range of product	Series 4




Complementary

Curve code	C
Number of poles	1
[In] rated current	20 A
Number of modules	1
[Ue] rated operational voltage	250 V
Breaking capacity	6 kA conforming to IEC 60947-2
Network type	DC
[Uimp] rated impulse withstand voltage	6 kV
Mechanical durability	20000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 1...25 mm ² rigid Screw terminal for 1 cable(s) 1...16 mm ² flexible Screw terminal for 1 cable(s) 1...16 mm ² flexible with ferrule
Wire stripping length	14 mm
Tightening torque	2.5 N.m

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Standards	AS/NZS 60898
Pollution degree	3
Relative humidity	95 % at 55 °C
Height	81 mm
Width	18 mm
Depth	78.5 mm
Net weight	128 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
