



### Main

Range	Clipsal
Product or component type	Ceiling light
Device application	Lighting
Market segment	Residential Small commercial

### Complementary

Device mounting	Surface
Shape	Round
Type of installation	Indoor
Rated power in W	20 W
Light source	LED
Total system power	240 V AC 50 Hz
Luminous flux	1300 Lm 1300 Lm 3000 K 4000 K 6000 K
Colour rendering index	R <sub>a</sub> =80
Bulb lifespan	30000 h
Beam angle	120 °
Load type	Dimmable LED
Device composition	Round white metal and plastic fixed integral dimming driver soft glow Light diffuser
Quantity per set	1
Trim width	330 mm
Trim height	80 mm
Net weight	1.0 kg

### Environment

IP degree of protection	IP20
Unified glare rating	< 22
Ambient air temperature for operation	-10...40 °C
Relative humidity	Non-condensing 10...95 % non-condensing

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.