

Product data sheet

Characteristics

NSYS3D4625T

Spacial S3D tspt door w/o mount.plate.
H400xW600xD250 IP66 IK08 RAL7035.



Main

| | |
|-----------------------------|---|
| Range | Spacial |
| Product name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure nominal height | 400 mm |
| Enclosure nominal width | 600 mm |
| Enclosure nominal depth | 250 mm |
| Door type | Glazed |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Standard |
| Installation accessory type | Wall-mounting |
| Device composition | 1 body 1 door 1 lock 1 cable gland plate |

Complementary

| | |
|-----------------------------|--|
| Body type | Single piece body Gutter-shaped front rail double sheet thickness |
| Number of doors | Front face: 1 door(s) |
| Door opening side | Reversible (120 °) |
| Lock type | 3 points lock, 3 mm double-bar |
| Accessibility for operation | Front |
| Removable parts | Door by hinges Cable gland plate by screws |
| Material | Body: steel Door: steel and security glass |
| Surface finish | Epoxy-polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product certifications | UL LR GL BV CUL DNV |
| Net weight | 11.82 kg |

Environment

| | |
|-------------------------------|-------------------------------------|
| Electromagnetic compatibility | Electromagnetic field immunity test |
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK08 conforming to IEC 62262 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|