

## Product data sheet

### Characteristics

# LC2D65AM7

## TeSys D reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 65 A - 220 V AC coil





## Principale

Gama	TeSys
Nume produs	TeSys D
Tip produs sau componenta	Contacteur reversibil
Nume scurt al dispozitivului	LC2D
Aplicatie contactor	Sarcina rezistiva Comanda motor
Categorie de utilizare	AC-3 AC-1
Prezentare dispozitiv	Preasamblat cu bare de alimentare pentru inversor
Descriere poli	3P
Power pole contact composition	3 NO
[Ue] tensiune nominala de functionare	Power circuit: $\leq 690$ V AC 25...400 Hz Power circuit: $\leq 300$ V DC
[Ie] curent nominal de utilizare	80 A (at $<60$ °C) at $\leq 440$ V AC AC-1 for power circuit 65 A (at $<60$ °C) at $\leq 440$ V AC AC-3 for power circuit
Putere motor kW	18,5 KW la 220...230 V c.a. 50 Hz 30 KW la 380...400 V c.a. 50 Hz 37 KW la 415...440 V c.a. 50 Hz 37 KW la 500 V c.a. 50 Hz 37 kW la 660...690 V c.a. 50 Hz
Motor power HP (UL / CSA)	40 Hp at 460/480 V AC 60 Hz for 3 phases motors 5 Hp at 115 V AC 60 Hz for 1 phase motors 10 Hp at 230/240 V AC 60 Hz for 1 phase motors 20 Hp at 200/208 V AC 60 Hz for 3 phases motors 20 Hp at 230/240 V AC 60 Hz for 3 phases motors 50 hp at 575/600 V AC 60 Hz for 3 phases motors
Tipul circuitului de comanda	AC at 50/60 Hz
[Uc] tensiune circuit de comanda	220 V AC 50/60 Hz
Compozitie contact auxiliar	1 NO + 1 NC
[Uimp] tensiune de tinere la impuls	6 kV conforming to IEC 60947
Categorie de supratensiune	III
[Ith] curent termic conventional in aer liber	10 A (at $60$ °C) for signalling circuit 80 A (at $60$ °C) for power circuit
Irms capacitatea nominala la inchidere	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 1000 A at 440 V for power circuit conforming to IEC 60947
Capacitate de rupere nominala	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] curent nominal de scurtcircuit admisibil	520 A $40$ °C - 10 s for power circuit 900 A $40$ °C - 1 s for power circuit 110 A $40$ °C - 10 min for power circuit 260 A $40$ °C - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Calibrul fuzibilului asociat	10 A gG for signalling circuit conforming to IEC 60947-5-1 125 A gG at $\leq 690$ V coordination type 1 for power circuit 125 A gG at $\leq 690$ V coordination type 2 for power circuit
Impedanta medie	1.5 mOhm - Ith 80 A 50 Hz for power circuit

[U <sub>i</sub> ] tensiune nominala de izolare	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
Durabilitate electrica	1,45 Mcycles 65 A AC-3 la U <sub>e</sub> ≤ 440 V 1,4 Mcycles 80 A AC-1 la U <sub>e</sub> ≤ 440 V
Puterea disipata pe pol	9.6 W AC-1 6.3 W AC-3
Front cover	Cu
Tip de blocare	Mecanic
Suport de montare	Placa Sina
Standarde	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Certificari produs	UL CCC CSA GOST
Conexiuni - borne	Control circuit: screw clamp terminals 1 cable(s) 1... 4 mm <sup>2</sup> flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1... 4 mm <sup>2</sup> flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1... 4 mm <sup>2</sup> flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1... 2.5 mm <sup>2</sup> flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1... 4 mm <sup>2</sup> solid Control circuit: screw clamp terminals 2 cable(s) 1... 4 mm <sup>2</sup> solid Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm <sup>2</sup> flexible without cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 1...25 mm <sup>2</sup> flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm <sup>2</sup> flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 1...25 mm <sup>2</sup> flexible with cable end Circuit electric conectori EverLink cu şurub BTR 1 cablu(ri) 1...35 mm <sup>2</sup> solid Circuit electric conectori EverLink cu şurub BTR 2 cablu(ri) 1...25 mm <sup>2</sup> solid
Cuplu de strangere	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Circuit electric 8 N.m - pornit conectori EverLink cu şurub BTR - cablu 25...35 mm <sup>2</sup> hexagonal 4 mm Circuit electric 5 N.m - pornit conectori EverLink cu şurub BTR - cablu 1...25 mm <sup>2</sup> hexagonal 4 mm
Timp de functionare	4...19 ms opening 12...26 ms closing
Nivel de incredere al securitatii	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Durabilitate mecanica	6 Mcycles
Viteza maxima de functionare	3600 cyc/h 60 °C

## Suplimentare

Tehnologie bobine	Fără modul de deparazitare inclus
Limite de tensiune circuit de comanda	0.3...0.6 Uc (-40...70 °C):drop-out AC 50/60 Hz 0.8...1.1 Uc (-40...60 °C):operational AC 50 Hz 0.85...1.1 Uc (-40...60 °C):operational AC 60 Hz 1...1.1 Uc (60...70 °C):operational AC 50/60 Hz
Consum de energie conectare in VA	140 VA 60 Hz cos phi 0.75 (at 20 °C) 160 VA 50 Hz cos phi 0.75 (at 20 °C)
Consum de energie mentinere in VA	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Disipare de caldura	4...5 W at 50/60 Hz
Tip contacte auxiliare	Type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 Type mirror contact 1 NC conforming to IEC 60947-4-1
Afisare frecventa circuit	25...400 Hz
Curentul minim de comutare	5 mA for signalling circuit
Tensiunea minima de comutare	17 V for signalling circuit
Timpul de nesuprapunere	1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Rezistenta de izolatie	> 10 MOhm for signalling circuit
Compatibilitatea contactelor	M2
Cod compatibilitate	LC2D
Motor power range	15...25 KW la 200...240 V 3 faze 30...50 KW la 380...440 V 3 faze 30...50 kW la 480...500 V 3 faze
Tip demaror motor	Reversing contactor
Tensiune contactor bobina	220 V c.a. standard

## Mediu

Grad de protectie IP	IP20 front face conforming to IEC 60529
Tratament protector	TH conforming to IEC 60068-2-30
Grad de poluare	3
Temperatura ambientala de utilizare	-40...60 °C 60...70 °C with derating
Temperatura de depozitare	-60...80 °C
Altitudinea de functionare	0...3000 m
Rezistenta la foc	850 °C conforming to IEC 60695-2-1
Intarziere flacara	V1 conforming to UL 94
Rezistenta mecanica	Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 4 Gn, 5...300 Hz Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms
Inaltime	122 mm
Latime	119 mm
Adancime	120 mm
Greutate produs	1,89 kg

## Unitati de impachetare

Tip unitate a formei de impachetare 1	PCE
Număr de produse în pachet	1
Greutate colet(Lbs)	2,067 kg
Inaltimea formei de impachetare 1	14 cm
Latimea formei de impachetare 1	16,2 cm
Lungimea formei de impachetare 1	19,8 cm
Greutatea formei de impachetare 2	8,8 kg
Greutatea formei de impachetare 3	44,424 kg

## Durabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	<a href="#">Declaratia REACH</a>
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform <a href="#">Declaratia RoHS UE</a>
Fara metale grele toxice	Da
Fara mercur	Da
Informatii privind scutirea de la RoHS	<a href="#">Da</a>
Regulamentul RoHS China	<a href="#">Declaratia RoHS China</a>
Raport de mediu	<a href="#">Profilul Ambiental Al Produsului</a>
Profil circularitate	<a href="#">Informatii Privind Sfarsitul Duratei De Viata</a>
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.
Fara PVC	Da

## Garanție contractuală

Garantie	18 months
----------	-----------