

Product data sheet

Characteristics

LA7D03Q

Thermal overload relays, TeSys Deca, remote electrical tripping, 380...400V AC



Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LR3D15.. LR3D35.. LR3D43.. LRD43.. LRD15.. LR2D LRD33.. LR3D33..
[Uc] control circuit voltage	380/400 V AC 50/60 Hz

Complementary

Maximum inrush power in VA	100 VA
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	4.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	105.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------