



### Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard Self-test
Supply	Non-maintained
Number of batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	Fluorescent tube G5 8 W LED 8 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

### Complementary

Range compatibility	Remote control
[Ue] rated operational voltage	220...230 V AC/DC 50 Hz
Power consumption in VA	4.1 VA
Power consumption in W	2.7 W 2.6 W
Current consumption	17 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Fresnel glass
Material	Housing: plastic Cover: plastic
Device mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Height	160 mm
Width	375 mm
Depth	68 mm

### Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	AENOR ENEC
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Packing Units

Package 1 Weight	1.23 kg
------------------	---------

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------