



Main

| | |
|-----------------------------|--|
| Device short name | OF SD SDE SDV |
| Product or component type | Auxiliary contact |
| Range compatibility | Compact NS630b...1600 Compact NS1600b...3200 Compact INS Compact INSE Compact INSJ Compact INV Compact NG Compact NR Compact NSX EasyPact CVS |
| Offer type | C5 C4 |
| Signal contacts composition | 1 NO/NC |

Complementary

| | |
|--|--|
| Auxiliary contacts type | Standard |
| Auxiliary contacts operation | Early-make Early-break |
| Mounting mode | Clip-on |
| [I _{th}] conventional free air thermal current | 6 A |
| [I _e] rated operational current | AC-12: 6 A at 110 V AC 50/60 Hz AC-12: 6 A at 220/240 V AC 50/60 Hz AC-12: 6 A at 24 V AC 50/60 Hz AC-12: 6 A at 380/440 V AC 50/60 Hz AC-12: 6 A at 48 V AC 50/60 Hz AC-12: 6 A at 480 V AC 50/60 Hz AC-12: 6 A at 660/690 V AC 50/60 Hz AC-15: 0.1 A at 660/690 V AC 50/60 Hz AC-15: 1.5 A at 480 V AC 50/60 Hz AC-15: 2 A at 380/440 V AC 50/60 Hz AC-15: 4 A at 220/240 V AC 50/60 Hz AC-15: 5 A at 110 V AC 50/60 Hz AC-15: 6 A at 24 V AC 50/60 Hz AC-15: 6 A at 48 V AC 50/60 Hz DC-12: 0.3 A at 250 V DC DC-12: 0.6 A at 110 V DC DC-12: 2.5 A at 48 V DC DC-12: 6 A at 24 V DC DC-14: 0.03 A at 250 V DC DC-14: 0.05 A at 110 V DC DC-14: 0.2 A at 48 V DC DC-14: 1 A at 24 V DC |
| Minimum load | 100 mA at 24 V |
| Width | 1 cm |
| Accessory / separate part category | Spare part for Compact NS630b...1600 Spare part for Compact NS1600b...3200 |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...70 °C |
| Ambient air temperature for storage | -25...70 °C |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 24 g |
| Package 1 Height | 2 cm |
| Package 1 width | 8.3 cm |
| Package 1 Length | 8.5 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 246 g |
| Package 2 Height | 11 cm |
| Package 2 width | 3 cm |
| Package 2 Length | 15 cm |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 300 |
| Package 3 Weight | 7.8 kg |
| Package 3 Height | 30 cm |
| Package 3 width | 30 cm |
| Package 3 Length | 40 cm |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|