

Osnovno

Ponuda	Fupact
Naziv proizvoda	Fupact ISFT
Skraćeno ime uređaja	ISFT630
Vrsta proizvoda ili dijela	Prekidač sa osiguračima
Namjena uređaja	Zaštita, nadzor i upravljanje Distribucija
Opis polova	3P
Number of fuse carriers	3
Tip rastalnog osigurača	DIN
Veličina rastalnog osigurača	NH3
Prikladnost za izolaciju	Da
Providni prekidač	Da
[Ithe] propisana termalna struja pri okolnoj temperaturi zraka	441 A 70 °C) vodoravno 441 A 70 °C) vertikalno 473 A 65 °C) vodoravno 473 A 65 °C) vertikalno 504 A 60 °C) vodoravno 504 A 60 °C) vertikalno 536 A 55 °C) vodoravno 536 A 55 °C) vertikalno 567 A 50 °C) vodoravno 567 A 50 °C) vertikalno 599 A 45 °C) vodoravno 599 A 45 °C) vertikalno 630 A 40 °C) 48 W 630 A 40 °C) vodoravno 630 A 40 °C) vertikalno
[Ithe] propisana termalna struja specifičnih kućišta	630 A 40 °C 48 W
[Ue] radni nazivni napon	440 V DC 690 V AC 50/60 Hz 800 V AC 50/60 Hz AC-20 800 V DC DC-20
[Ui] nazivni napon izolacije	800 V AC 50/60 Hz 800 V DC
[Uimp] nazivni impulsni podnosivi napon	8 kV
[Ie] nazivna pogonska struja	AC-21B: 630 A at 220/240 V AC 50/60 Hz AC-21B: 630 A at 380/415 V AC 50/60 Hz AC-21B: 630 A at 440/480 V AC 50/60 Hz AC-21B: 630 A at 500 V AC 50/60 Hz AC-21B: 630 A at 660/690 V AC 50/60 Hz AC-22B: 630 A at 220/240 V AC 50/60 Hz AC-22B: 630 A at 380/415 V AC 50/60 Hz DC-21B: 630 A at 125 V DC (1 pol) DC-21B: 630 A at 220 V DC (1 pol) DC-21B: 630 A at 440 V DC (2 pola u seriji)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Dodatno

[Icm] Rated short-circuit making capacity	Icm 105 kA 500 V Icm 105 kA 690 V Icn 50 kA 500 V Icn 50 kA 690 V Icm 105 kA 415 V Icn 50 kA 415 V
Nazivni rad	Neprekidni
Tip upravljanja	Ručka nosača osigurača
Dodatak za zaključavanje	3 lokota
Monterški držač	Montažna ploča
Mjesto za montažu	Usporedno
Operacija kontakta	Jednstruko prekidanje
Mehanička izdržljivost	1000 ciklus/a
Električna izdržljivost	AC-21B 200 ciklus/a 690 V AC 50/60 Hz AC-22B 200 ciklus/a 415 V AC 50/60 Hz
Priključci - stezaljke	Vijčani spoj M10 630 A
Širina	250 mm
Visina	271 mm
Dubina	132 mm
Standardi	IEC 60269-2-1 EN/IEC 60947-1 EN/IEC 60947-3
Certifikati proizvoda	KEMA-KEUR

Okolina

IP stupanj zaštite	IP20 conforming to IEC 60529
IK stupanj zaštite	IK07u skladu s EN 50102
Stupanj onečišćenja	3 u skladnosti sa IEC 60947
Okolišna temperatura zraka pri radu	-25...70 °C
Okolišna temperatura zraka pri skladištenju	-50...85 °C

Broj pakirnih jedinica

Mjerna jedinica Paketa 1	PCE
Broj Jedinica u Paketu 1	1
Paket 1 Visina	16,000 cm
Paket 1 Širina	21,000 cm
Paket 1 Dužina	27,000 cm
Paket 1 Težina	4,102 kg
Mjerna jedinica Paketa 2	P12
Broj Jedinica u Paketu 2	8
Paket 2 Visina	50,000 cm
Paket 2 Širina	80,000 cm
Paket 2 Dužina	120,000 cm
Paket 2 Težina	50,520 kg

Održivost ponude

Direktiva EU RoHS	Sukladno  Izjava EU RoHS
Bez otrovnih teških metala	Da
Bez žive	Da
Propis RoHS za Kinu	 Izjava RoHS Za Kinu
Informacije o RoHS izuzeću	 Da
Izjava o očuvanju okoliša	 Ekološki Profil Proizvoda

Profil cirkularnosti	Nema potrebe za specifičnim operacijama recikliranja
WEEE	Proizvod se na tržištima EU mora odlagati u skladu sa specifičnim propisima o prikupljanju otpada; nikako se ne smije odlagati s komunalnim otpadom.

Ugovorno jamstvo

Jamstvo	18 months
---------	-----------